

## POWDER FREE NITRILE GLOVES MEDICAL GRADE

# INS-GL-NIT5-100

The NITRO 5 nitrile gloves offer superior quality protection for medical applications.

With a thickness of 5.0 mil, these gloves are a wise choice for any professional in need of reliable and durable protection. Made from high-quality materials, they offer superior resistance to tearing, punctures, and chemicals, making them ideal for use in high-risk environments.

Their blue color makes them easily identifiable for use in medical settings. Whether you work in the food, medical, automotive, or any other industry requiring adequate protection, these powder-free gloves are designed for a comfortable fit and maximum dexterity, while providing reliable protection.



### FEATURES

- 100 gloves/box
  - Textured finish for better dexterity
  - For single use only
  - Rolled cuff keeps the glove snug at the wrist and prevents liquid from entering.
  - High resistance
  - Latex-free
  - Hypoallergenic
  - Non-sterile
  - Ambidextrous
  - Each batch of gloves is air-tested to detect pinholes
  - Chemotherapy-tested
- 
- Compliance with ASTM D6319:00a standard
  - ISO 9001 and ISO 13485 quality assurance
  - Health Canada Approved.

### INDUSTRIES WHERE MOST USED



DIMENSIONS		
Code + Size	Palm width (mm)	Length (mm)
INS-GL-NIT5-100S	80-89	Min.240
INS-GL-NIT5-100M	90-99	Min.240
INS-GL-NIT5-100L	100-109	Min.240
INS-GL-NIT5-100XL	110-119	Min.240

THICKNESS	
Measured part	Single wall (mm)
Finger	min. 0.13
Palm	min. 0.11
Cuff	min. 0.05

PHYSICAL PROPERTIES		
Property	Unaged	Aged
TENSILE STRENGTH	min.14 Mpa	min.14 Mpa
ELONGATION	min.500 %	min.500 %
FORCE AT BREAK	min.6 N	min.6 N

### INSTRUCTION FOR USE

Before putting on gloves hands must be clean and dry. Gloves do not replace the need for hand hygiene. Hands must be washed every time gloves are removed to avoid contamination. Gloves are for single use. Reuse of gloves has been associated with transmission of antibiotic-resistant organisms. Change gloves if moving from a contaminated area to a non-contaminated area. Be sure to wear gloves that fit properly, gloves should fit snugly around wrists and hands. Different sizes are available.

100 pieces per box, 10 boxes per shipping carton. Store in a cool, dry place. Avoid excessive heat (40°C, 104°F). Shield open boxes from direct sun and fluorescent lighting. To order, please refer to a specific size and mention the product code.